

Fulflo® NP Filter Vessels

■ Natural Polypropylene

Single Cartridge Filter Vessel Series

Fulflo® Natural Polypropylene Vessels for High Purity Applications

Parker's Fulflo NP series vessels feature pure natural polypropylene construction. The NP series is an ideal economical alternative to stainless steel and fluoropolymer vessels for filtration of corrosive fluids. They are essential for applications and processes demanding high purity filtration. Availability of 10 inch and 20 inch lengths and both single and double-open-end seal designs adds additional versatility.

Markets

- Electronics
- Pharmaceutical
- Chemical Process
- Photographic
- Electroplating
- Pure Water
- Food & Beverage

Applications

- Electronic Grade Chemicals
- Process Gases
- Organic Solvents
- Photographic Solutions
- Inorganic Chemicals
- DI Water
- Potable & Edible Fluids



Features and Benefits

- Fulflo NP series vessels available in two lengths and two seal designs offer versatility.
- Several O-ring options maximize compatibility choices. Viton is standard.
- Smooth fluid contact surfaces prevent bacteria and contaminant build-up.
- U-bracket available for pipe mounting.
- Mounting bosses in head accommodate L-bracket.
- Securely retained head-to-shell O-ring ensures effective sealing by positive tangential contact and eliminates accidental misalignment.
- Positive head-to-shell "stop" prevents overtightening.
- Individual packaging ensures cleanliness until use.
- NP vessels accept all standard double-open-end and single-open-end 2-222 O-ring design Fulflo filter cartridges.
- NP vessels of pure polypropylene meet FDA requirements for edible and potable liquid filtration.
- Available with pressure relief vent or threaded vent and drain.
- Service wrenches available for easy installation.
- NP vessels totally incinerable after useful life.

Process Filtration Division

WARNING! FAILURE OR IMPROPER SELECTION OR IMPROPER USE OF THE PRODUCTS AND/OR SYSTEMS DESCRIBED HEREIN OR RELATED ITEMS CAN CAUSE DEATH, PERSONAL INJURY AND PROPERTY DAMAGE. This document and other information from Parker Hannifin Corporation, its subsidiaries and authorized distributors provide product and/or system options for further investigation by users having technical expertise. It is important that you analyze all aspects of your application and review the information concerning the product or system in the current product catalogue. Due to the variety of operating conditions and applications for these products or systems, the user, through its own analysis and testing, is solely responsible for making the final selection for the products and systems and assuring that all performance, safety and warning requirements of the application are met. The products described herein, including without limitation, product features, specifications, designs, availability and pricing, are subject to change by Parker Hannifin Corporation and its subsidiaries at any time without notice.



Single Cartridge Filter Vessel Series

Specifications

Materials of Construction:

- Vessel: 100% natural FDA grade polypropylene
- Head-to-shell 2-240 O-Ring:
 - Standard (Industrial Grade): Viton
 - Optional (FDA Grade): Buna-N, EPDM, Silicone
- Pressure Relief Button O-Ring: Buna-N only

Maximum Recommended Operating Conditions:

- Temperature: 125°F (52°C)
- Pressure: 150 psi (10.3 bar)
- Flow Rate: 23 l/min (0.2 psid) for 10 in vessel; 46 l/min (0.9 psid) for 20 in vessel

Recommended Cartridge Dimensions:

- NP10: 2³/₈ in (60.3mm) to 2³/₄ in (70mm) O.D. x 1 in (25.4mm) I.D. x 9⁵/₈ in (244mm) to 9¹³/₁₆ in (249mm) long
- NP20: 2³/₈ in (60.3mm) to 2³/₄ in (70mm) O.D. x 1 in (25.4mm) I.D. x 19⁷/₈ in (505mm) to 20¹/₁₆ in (510mm) long

Connection Dimensions:

- Inlet/Outlet: 3/4 in NPTF/BSP
- Vent/Drain: 1/4 in NPTF/BSP

Cartridge Seal Designs:

- "TC": Single-Open-End with 222 O-ring receptacle
- "DO": Double-Open-End with knife edge seal; also accepts 213 O-ring seal cartridge (PR code)

■ Vessel Assembly Dimensions:

Housing with pressure relief button

Housing without pressure relief button

Housing with 1/4" NPT vent and drain

■ Standard Vessel Assemblies:

NP10-DO-N-V	NP20-DO-N-V
NP10-DO-R-V	NP20-DO-R-V
NP10-DO-DV-V	NP20-DO-DV-V
NP10-TC-N-V	NP20-TC-N-V
NP10-TC-R-V	NP20-TC-R-V
NP10-TC-DV-V	NP20-TC-DV-V

■ Compatible Semi-Conductor Chemicals (52°C max. temp.):

Acetic Acid 50%
Acetone 99.5%
Ammonium Fluoride 40%
Ammonium Hydroxide 10%
Hydrochloric Acid 37%
Hydrofluoric Acid 49%, 52%
Nitric Acid 10%
Phosphoric Acid 85%
Potassium Hydroxide 45%
Sodium Hydroxide 50%
Tetrachloroethylene 99.0%

Ordering Information

NP	10	TC*	DV	V	B
Vessel Type	Shell Length	Cartridge Seal Design	Vent/Drain Options	Head-to-Shell 222 O-Ring	Thread
Natural Polypropylene	10 = 254mm 20 = 508mm	DO = Double-Open-End (gasket seal) TC = Single-Open-End (222 O-ring seal)	D = 1/4 in Female NPT Drain (Plugged) N = No Vent, Drain or Pressure Relief Button R = Pressure Relief Button* V = 1/4 in Female NPT Vent (Plugged)	E = EPDM (FDA Grade) N = Buna-N (FDA Grade) S = Silicone (FDA Grade) V = Viton (Industrial Grade)	No Symbol = NPT B = BSP
* Pressure Relief Button ("R") not recommended for hazardous fluid applications.					

Process Filtration Division

Parker Filtration
Filter Division Europe
Shaw Cross Business Park
Dewsbury, West Yorkshire
WF12 7RD, England
Phone: +44 (0) 1924 487000
Fax: +44 (0) 1924 487001
Website: www.parker.com

